




## Lighting element for surface-mounted housing



Spezifikation	Bestell-Nr.	VE	GBP/Stück o. MWSt.	PS	EAN
 cream white glossy	1067 01	1/5	23.55	02	4010337105169
 pure white glossy	1067 03	1/5	23.55	02	4010337107088
 black matt	1067 005	1/5	27.10	02	4010337110255

## Merkmale

- The white LEDs project a light corridor downwards. This produces indirect orientation light that also avoids bothersome glare in bedrooms.

## Technische Daten

Rated voltage:	AC 230 V, 50 Hz
Power consumption:	0.05 W / 1.65 mA
Light intensity:	0.2 cd
Ambient temperature:	0 °C to +40 °C