










Gira E2 cover frame with inscription space anthracite



Spezifikation	Bestell-Nr.	VE	GBP/Stück o. MWSt.	PS	EAN
 1-gang	1091 23	1/10	11.02	11	4010337084044
 2-gang horizontal	1092 23	1/10	18.01	11	4010337084099
 2-gang vertical	1102 23	1/10	18.01	11	4010337089148
 3-gang horizontal	1093 23	1/5	29.43	11	4010337084174
 3-gang vertical	1103 23	1/5	29.43	11	4010337084211
 4-gang horizontal	1094 23	1/5	44.34	11	4010337084259
 4-gang vertical	1114 23	1/5	44.34	11	4010337084297
 5-gang horizontal	1095 23	1/5	63.51	11	4010337084372
 5-gang vertical	1115 23	1/5	63.51	11	4010337084334

Merkmale

- Shatter-proof.
 - Spray-proof.
 - Frames with transparent view window for inscription.
 - Ideally suited for use in buildings in which the electrical installation must be identified and documented, for example in administrations, commercial operations, airports, companies, and hospitals.
 - Plastic: halogen-free, impact-resistant and shatter-proof thermoplastic" or would that then be polycarbonate.
-

Hinweise

- Not to be used with: sealing kit IP44, surface-mounted housing with flat design, surface-mounted housing.
-