











Gira E2 cover frame with inscription space grey matt



Spezifikation	Bestell-Nr.	VE	GBP/Stück o. MWSt.	PS	EAN
 1-gang	1091 37	1/10	15.03	11	4010337082590
 2-gang horizontal	1092 37	1/10	24.62	11	4010337082651
 2-gang vertical	1102 37	1/10	24.62	11	4010337082699
 3-gang horizontal	1093 37	1/5	39.37	11	4010337082668
 3-gang vertical	1103 37	1/5	39.37	11	4010337082729
 4-gang horizontal	1094 37	1/5	60.70	11	4010337082675
 4-gang vertical	1114 37	1/5	60.70	11	4010337082873
 5-gang horizontal	1095 37	1/5	88.37	11	4010337082682
 5-gang vertical	1115 37	1/5	88.37	11	4010337082880

Merkmale

- Shatter-proof.
 - Spray-proof.
 - Frames with transparent view window for inscription.
 - Ideally suited for use in buildings in which the electrical installation must be identified and documented, for example in administrations, commercial operations, airports, companies, and hospitals.
 - Plastic: halogen-free, impact-resistant and shatter-proof thermoplastic" or would that then be polycarbonate.
-

Hinweise

- Not to be used with: sealing kit IP44, surface-mounted housing with flat design, surface-mounted housing.
-