










Gira E2 cover frame with inscription space colour aluminium



Spezifikation	Bestell-Nr.	VE	GBP/Stück o. MWSt.	PS	EAN
 1-gang	1091 25	1/10	15.03	11	4010337084051
 2-gang horizontal	1092 25	1/10	24.62	11	4010337084112
 2-gang vertical	1102 25	1/10	24.62	11	4010337084143
 3-gang horizontal	1093 25	1/5	39.37	11	4010337084181
 3-gang vertical	1103 25	1/5	39.37	11	4010337084228
 4-gang horizontal	1094 25	1/5	60.70	11	4010337084266
 4-gang vertical	1114 25	1/5	60.70	11	4010337084303
 5-gang horizontal	1095 25	1/5	88.37	11	4010337084389
 5-gang vertical	1115 25	1/5	88.37	11	4010337084341

Merkmale

- Shatter-proof.
 - Spray-proof.
 - Frames with transparent view window for inscription.
 - Ideally suited for use in buildings in which the electrical installation must be identified and documented, for example in administrations, commercial operations, airports, companies, and hospitals.
 - Plastic: halogen-free, impact-resistant and shatter-proof thermoplastic" or would that then be polycarbonate.
-

Hinweise

- Not to be used with: sealing kit IP44, surface-mounted housing with flat design, surface-mounted housing.
-