GIRA Data sheet

© Copyright by
Gira Giersiepen GmbH & Co. KG
All rights reserved

www.gira.com

Gira Standard 55 cover frame with inscription space pure white glossy

Specification	Order No.	Packing unit	GBP/piece without VAT	PS	EAN
 1-gang	1091 03	1/10	6.64	01	4010337091035
 2-gang horizontal	1092 03	1/10	12.32	01	4010337092032
 2-gang vertical	1102 03	1/10	12.32	01	4010337102038
3-gang horizontal	1093 03	1/10	19.40	01	4010337093039
 3-gang vertical	1103 03	1/5	19.40	01	4010337103035
 4-gang horizontal	1094 03	1/5	28.27	01	4010337094036
 4-gang vertical	1114 03	1/5	28.27	01	4010337008910
 5-gang horizontal	1095 03	1/5	42.50	01	4010337095033
 5-gang vertical	1115 03	1/5	42.50	01	4010337115038

Illustrations are similar and may deviate from originals.
Prices valid for United Kingdom with prices valid 01/26.

© Copyright by
Gira Giersiepen GmbH & Co. KG
All rights reserved

Features

- Plastic: halogen-free, impact-resistant and shatter-proof thermoplastic” or would that then be polycarbonate.
- Spray-proof.
- Frames with transparent view window for inscription.
- Ideally suited for use in buildings in which the electrical installation must be identified and documented, for example in administrations, commercial operations, airports, companies, and hospitals.

Notes

- Not to be used with: surface-mounted housing with flat design, surface-mounted housing.
