

Gira Standard 55 cover frame with inscription space pure white matt



Spezifikation	Bestell-Nr.	VE	GBP/Stück o. MWSt.	PS	EAN
 1-gang	1091 27	1/10	6.64	01	4010337091271
 2-gang horizontal	1092 27	1/10	12.32	01	4010337092278
 2-gang vertical	1102 27	1/10	12.32	01	4010337102274
 3-gang horizontal	1093 27	1/5	19.40	01	4010337093275
 3-gang vertical	1103 27	1/5	19.40	01	4010337103271
 4-gang horizontal	1094 27	1/5	28.27	01	4010337094272
 4-gang vertical	1114 27	1/5	28.27	01	4010337008927
 5-gang horizontal	1095 27	1/5	42.50	01	4010337095279
 5-gang vertical	1115 27	1/5	42.50	01	4010337115274

Merkmale

- Plastic: halogen-free, impact-resistant and shatter-proof thermoplastic" or would that then be polycarbonate.
 - Spray-proof.
 - Frames with transparent view window for inscription.
 - Ideally suited for use in buildings in which the electrical installation must be identified and documented, for example in administrations, commercial operations, airports, companies, and hospitals.
-

Hinweise

- Not to be used with: sealing kit IP44, surface-mounted housing with flat design, surface-mounted housing.
-