

Gira E2 cover frame with inscription space pure white glossy



| Specification                                                                                         | Order No. | Packing unit | GBP/piece<br>without VAT | PS | EAN           |
|-------------------------------------------------------------------------------------------------------|-----------|--------------|--------------------------|----|---------------|
|  1-gang             | 1091 29   | 1/10         | 10.68                    | 01 | 4010337084068 |
|  2-gang horizontal | 1092 29   | 1/10         | 16.97                    | 01 | 4010337084129 |
|  2-gang vertical   | 1102 29   | 1/10         | 16.97                    | 01 | 4010337084150 |
|  3-gang horizontal | 1093 29   | 1/5          | 28.58                    | 01 | 4010337084198 |
|  3-gang vertical   | 1103 29   | 1/5          | 28.58                    | 01 | 4010337084235 |
|  4-gang horizontal | 1094 29   | 1/5          | 43.01                    | 01 | 4010337084273 |
|  4-gang vertical   | 1114 29   | 1/5          | 43.01                    | 01 | 4010337084310 |
|  5-gang horizontal | 1095 29   | 1/5          | 61.62                    | 01 | 4010337084396 |
|  5-gang vertical   | 1115 29   | 1/5          | 61.62                    | 01 | 4010337084358 |

Illustrations are similar and may deviate from originals.  
Prices valid for United Kingdom with prices valid 01/26.

## Features

- Shatter-proof.
  - Spray-proof.
  - Frames with transparent view window for inscription.
  - Ideally suited for use in buildings in which the electrical installation must be identified and documented, for example in administrations, commercial operations, airports, companies, and hospitals.
  - Plastic: halogen-free, impact-resistant and shatter-proof thermoplastic" or would that then be polycarbonate.
- 

## Notes

- Not to be used with: surface-mounted housing with flat design, surface-mounted housing.
-