










## Gira E2 cover frame with inscription space black matt



Spezifikation	Bestell-Nr.	VE	GBP/Stück o. MWSt.	PS	EAN
 1-gang	1091 09	1/10	15.03	11	4010337036746
 2-gang horizontal	1092 09	1/10	24.62	11	4010337036814
 2-gang vertical	1102 09	1/10	24.62	11	4010337036807
 3-gang horizontal	1093 09	1/5	39.37	11	4010337036852
 3-gang vertical	1103 09	1/5	39.37	11	4010337036845
 4-gang horizontal	1094 09	1/5	60.70	11	4010337036890
 4-gang vertical	1114 09	1/5	60.70	11	4010337036883
 5-gang horizontal	1095 09	1/5	88.37	11	4010337036920
 5-gang vertical	1115 09	1/5	88.37	11	4010337036913

## **Merkmale**

- Shatter-proof.
  - Spray-proof.
  - Frames with transparent view window for inscription.
  - Ideally suited for use in buildings in which the electrical installation must be identified and documented, for example in administrations, commercial operations, airports, companies, and hospitals.
  - Plastic: halogen-free, impact-resistant and shatter-proof thermoplastic" or would that then be polycarbonate.
- 

## **Hinweise**

- Not to be used with: sealing kit IP44, surface-mounted housing with flat design, surface-mounted housing.
-