










## Gira E2 cover frame with inscription space anthracite



| Spezifikation   | Bestell-Nr. | VE   | GBP/Stück o. MWSt. | PS | EAN           |
|---|-------------|------|--------------------|----|---------------|
|  1-gang              | 1091 23     | 1/10 | 11.02              | 11 | 4010337084044 |
|  2-gang horizontal | 1092 23     | 1/10 | 18.01              | 11 | 4010337084099 |
|  2-gang vertical   | 1102 23     | 1/10 | 18.01              | 11 | 4010337089148 |
|  3-gang horizontal | 1093 23     | 1/5  | 29.43              | 11 | 4010337084174 |
|  3-gang vertical   | 1103 23     | 1/5  | 29.43              | 11 | 4010337084211 |
|  4-gang horizontal | 1094 23     | 1/5  | 44.34              | 11 | 4010337084259 |
|  4-gang vertical   | 1114 23     | 1/5  | 44.34              | 11 | 4010337084297 |
|  5-gang horizontal | 1095 23     | 1/5  | 63.51              | 11 | 4010337084372 |
|  5-gang vertical   | 1115 23     | 1/5  | 63.51              | 11 | 4010337084334 |

## **Merkmale**

- Shatter-proof.
  - Spray-proof.
  - Frames with transparent view window for inscription.
  - Ideally suited for use in buildings in which the electrical installation must be identified and documented, for example in administrations, commercial operations, airports, companies, and hospitals.
  - Plastic: halogen-free, impact-resistant and shatter-proof thermoplastic" or would that then be polycarbonate.
- 

## **Hinweise**

- Not to be used with: sealing kit IP44, surface-mounted housing with flat design, surface-mounted housing.
-