


External camera



Spezifikation	Bestell-Nr.	VE	GBP/Stück o. MWSt.	PS	EAN
 pure white	1220 00	1	554.43	10	4010337100058

Merkmale

- External camera for wall or ceiling mounting with variable lens, integrated IR LED illumination, and automatic white balance.
- The camera can be installed anywhere in the entrance area and be integrated into the Gira door communication system using the DCS camera gateway.
- Light-sensitive chip set for clear imaging in low-light conditions.
- Switchable IR LEDs for video monitoring in complete darkness.
- Camera module and housing for easy, rapid installation.
- Camera module adjustable on three axes.

Technische Daten

Rated voltage:	DC 12 V +10 %
Current consumption	
- DC 12 V:	max. 500 mA
Connections:	1 x video (HD TVI, BNC), 1 x video (FBAS, BNC), 1 x power supply (DC)
Camera	
- Image sensor:	1/2.9" CMOS progressive scan
- Type:	Variable, manual
- Lens:	2.8 to 12 mm
- Resolution:	480 TVL
- Horizontal angle of vision:	28° to 85°
Day/night switching:	Electromechanical IR cut filter
Electronic shutter control:	1/50 to 1/50 000 s
Camera control:	On-screen display (OSD), joystick on cable
Minimal lighting	
- Day:	0.05 lx
- IR mode:	0 lx
IR LED:	24 LED

GIRA Parts list

catalogue.gira.com

© Copyright by
Gira Giersiepen GmbH & Co. KG
All rights reserved

www.gira.com

IR range:	20 m
Ambient temperature:	-20 °C to +60 °C
Protection class:	IP66
Humidity:	max. 90%
Weight:	approx. 660 g
Dimensions - External camera:	Dia. 126, H 100.3 mm
