© Copyright by
Gira Giersiepen GmbH & Co. KG
All rights reserved



**External camera**



| Specification | Order No. | Packing unit | GBP/piece without VAT | PS | EAN |
|---|---|---|---|---|---|
|  pure white | 1220 00 | 1 | 554.43 | 10 | 4010337100058 |

**Features**

- External camera for wall or ceiling mounting with variable lens, integrated IR LED illumination, and automatic white balance.
- The camera can be installed anywhere in the entrance area and be integrated into the Gira door communication system using the DCS camera gateway.
- Light-sensitive chip set for clear imaging in low-light conditions.
- Switchable IR LEDs for video monitoring in complete darkness.
- Camera module and housing for easy, rapid installation.
- Camera module adjustable on three axes.

**Technical data**

| | |
|---|---|
| Rated voltage: | DC 12 V +10 % |
| Current consumption | |
| - DC 12 V: | max. 500 mA |
| Connections: | 1 x video (HD TVI, BNC), 1 x video (FBAS, BNC), 1 x power supply (DC) |
| Camera | |
| - Image sensor: | 1/2.9" CMOS progressive scan |
| - Type: | Variable, manual |
| - Lens: | 2.8 to 12 mm |
| - Resolution: | 480 TVL |
| - Horizontal angle of vision: | 28° to 85° |
| Day/night switching: | Electromechanical IR cut filter |
| Electronic shutter control: | 1/50 to 1/50 000 s |
| Camera control: | On-screen display (OSD), joystick on cable |
| Minimal lighting | |
| - Day: | 0.05 lx |
| - IR mode: | 0 lx |

Illustrations are similar and may deviate from originals.
Prices valid for United Kingdom with prices valid 01/26.

© Copyright by
Gira Giersiepen GmbH & Co. KG
All rights reserved



| | |
|---|---|
| IR LED: | 24 LED |
| IR range: | 20 m |
| Ambient temperature: | -20 °C to +60 °C |
| Protection class: | IP66 |
| Humidity: | max. 90% |
| Weight: | approx. 660 g |
| Dimensions<br>- External camera: | Dia. 126, H 100.3 mm |