© Copyright by
Gira Giersiepen GmbH & Co. KG
All rights reserved



**Door station, 3-gang TX_44**



| Specification | | Order No. | Packing unit | GBP/piece without VAT | PS | EAN |
|---|---|---|---|---|---|---|
|  | pure white | 1261 66 | 1 | 321.33 | 18 | 4010337261667 |
|  | anthracite (lacquered) | 1261 67 | 1 | 330.70 | 18 | 4010337261674 |
|  | colour aluminium (lacquered) | 1261 65 | 1 | 330.70 | 18 | 4010337261650 |

**Features**

- Installation in a conventional flush-mounted device box.
- Fits in the cover frames of the Gira TX_44 switch range.
- Modular design, therefore easy installation and expandability with further components such as call buttons, info module, colour camera, Keyless In.
- Signal transmission and supply of the audio and video components via reverse-polarity-protected and short-circuit-proof 2-wire bus.
- One-man commissioning with simple commissioning procedure.
- Weather-resistant loudspeaker.
- High-quality electret microphone.
- Hands-free feature (voice-controlled talk-back with echo and background noise suppression).
- Call-button illumination with LED technology, light colour white. Even, clearly visible call button illumination is achieved via maintenance-free, energy-saving LED technology.
- Acknowledgement tone when call button is pressed.
- Voice volume adjustable.
- Sprayed-water proof call-button cover plate made of shock-resistant plastic.
- Name plate of the call button can be exchanged without tools and frame removal.
- Professional inscription by the Gira inscription servicewww.beschriftung.gira.deor the Gira inscription software.
- Binary input for connecting a zero-voltage push button (NO contact) as a call button.
- Call button, 3-gang

**Technical data**

| | |
|---|---|
| Power supply: | via the 2-wire bus |
| Bus coupler connections | |
| - 2-wire bus: | 2 x screw terminal |

Illustrations are similar and may deviate from originals.
Prices valid for United Kingdom with prices valid 01/26.

© Copyright by
Gira Giersiepen GmbH & Co. KG
All rights reserved



| | |
|---|---|
| - Additional power supply: | 2 x screw terminal |
| - Binary input: | 2 x screw terminal |
| - Connection cable: | 2 x connector strip |
| - Video: | 1 x connector strip |
| Speech insert connections | |
| - Connection cable: | 2 x connector strip |
| Ambient temperature: | -25 °C to +70 °C |
| Protection class: | IP44 |
| Installation depth: | 30 mm |
| Dimensions | |
| - Name plates: | W 62 x H 18 mm |

---

**Notes**

- If only two call buttons are required, please use the call-button cover plate for call button, 3-gang.

---