© Copyright by
Gira Giersiepen GmbH & Co. KG
All rights reserved

Door station, 3-gang TX_44



Specification		Order No.	Packing unit	GBP/piece without VAT	PS	EAN
	pure white	1261 66	1	321.33	18	4010337261667
	anthracite (lacquered)	1261 67	1	330.70	18	4010337261674
	colour aluminium (lacquered)	1261 65	1	330.70	18	4010337261650

Features

- Installation in a conventional flush-mounted device box.
- Fits in the cover frames of the Gira TX_44 switch range.
- Modular design, therefore easy installation and expandability with further components such as call buttons, info module, colour camera, Keyless In.
- Signal transmission and supply of the audio and video components via reverse-polarity-protected and short-circuit-proof 2-wire bus.
- One-man commissioning with simple commissioning procedure.
- Weather-resistant loudspeaker.
- High-quality electret microphone.
- Hands-free feature (voice-controlled talk-back with echo and background noise suppression).
- Call-button illumination with LED technology, light colour white. Even, clearly visible call button illumination is achieved via maintenance-free, energy-saving LED technology.
- Acknowledgement tone when call button is pressed.
- Voice volume adjustable.
- Sprayed-water proof call-button cover plate made of shock-resistant plastic.
- Name plate of the call button can be exchanged without tools and frame removal.
- Professional inscription by the Gira inscription servicewww.beschriftung.gira.deor the Gira inscription software.
- Binary input for connecting a zero-voltage push button (NO contact) as a call button.
- Call button, 3-gang

Technical data

Power supply:	via the 2-wire bus
Bus coupler connections	
- 2-wire bus:	2 x screw terminal

Illustrations are similar and may deviate from originals.
Prices valid for United Kingdom with prices valid 01/26.

© Copyright by
Gira Giersiepen GmbH & Co. KG
All rights reserved

- Additional power supply:	2 x screw terminal
- Binary input:	2 x screw terminal
- Connection cable:	2 x connector strip
- Video:	1 x connector strip
Speech insert connections	
- Connection cable:	2 x connector strip
Ambient temperature:	-25 °C to +70 °C
Protection class:	IP44
Installation depth:	30 mm
Dimensions	
- Name plates:	W 62 x H 18 mm

Notes

- If only two call buttons are required, please use the call-button cover plate for call button, 3-gang.
