© Copyright by
Gira Giersiepen GmbH & Co. KG
All rights reserved



**Call button, 1 gang for door station TX_44**



| Specification | Order No. | Packing unit | GBP/piece without VAT | PS | EAN |
|---|---|---|---|---|---|
|  Program-neutral | 1262 00 | 1 | 153.15 | 18 | 4010337262008 |

**Features**

- Installation in a conventional flush-mounted device box.
- Fits in the cover frames of the Gira TX_44 switch range.
- Modular design, allowing easy installation and expandability.
- Signal transmission and supply of the audio and video components via reverse-polarity-protected and short-circuit-proof 2-wire bus.
- The door station can be expanded with an additional call button (up to 14 call button inserts, 1- or 3-gang can be connected to one door station).
- Call-button illumination with LED technology, light colour white. Even, clearly visible call button illumination is achieved via maintenance-free, energy-saving LED technology.
- Sprayed-water proof call-button cover plate made of shock-resistant plastic.
- Name plate can be replaced without tools and without removing the frame.
- Professional inscription by the Gira inscription servicewww.beschriftung.gira.deor the Gira inscription software.

**Technical data**

| | |
|---|---|
| Connecting the connection cable: | 2 x connector strip |
| Protection class: | IP44 |
| Power supply: | via connection cable |
| Ambient temperature: | -25 °C to +70 °C |
| Installation depth: | 30 mm |
| Dimensions<br>- Name plate: | W 62 x H 62 mm |

Illustrations are similar and may deviate from originals.
Prices valid for United Kingdom with prices valid 01/26.