© Copyright by
Gira Giersiepen GmbH & Co. KG
All rights reserved

Info module for door station TX_44



Specification	Order No.	Packing unit	GBP/piece without VAT	PS	EAN
Program-neutral	1264 00	1	135.41	18	4010337264002

Features

- Installation in a conventional flush-mounted device box.
- Fits in the cover frames of the Gira TX_44 switch range.
- Modular design, allowing easy installation and expandability.
- Signal transmission and supply of the audio and video components via reverse-polarity-protected and short-circuit-proof 2-wire bus.
- Expansion of the door station by an info module for display of the house number, name, or other information.
- Backlighting with LED technology, light colour white. Steady, clearly visible illumination is achieved using maintenance-free, energy-saving LED technology.
- Sprayed-water proof cover plate made of shock-resistant plastic.
- Inscription space can be replaced without tools and without removing the frame.
- Professional inscription by the Gira inscription servicewww.beschriftung.gira.deor the Gira inscription software.

Technical data

Connecting the connection cable:	2 x connector strip
Protection class:	IP44
Power supply:	via connection cable
Ambient temperature:	-25 °C to +70 °C
Installation depth:	30 mm
Dimensions - Information sign:	W 62 x H 62 mm

Illustrations are similar and may deviate from originals.
Prices valid for United Kingdom with prices valid 01/26.