© Copyright by
Gira Giersiepen GmbH & Co. KG
All rights reserved

www.gira.com

**Surface-mounted door station, 1 gang**



| Specification | | Order No. | Packing unit | GBP/piece without VAT | PS | EAN |
|---|---|---|---|---|---|---|
|  | pure white | 1266 66 | 1 | 268.43 | 18 | 4010337266662 |
|  | anthracite (lacquered) | 1266 67 | 1 | 278.15 | 18 | 4010337266679 |
|  | colour aluminium (lacquered) | 1266 65 | 1 | 278.15 | 18 | 4010337266655 |

**Features**

- Fully pre-assembled surface-mounted door station for vertical surface-mounted installation. This facilitates fast and clean installation.
- In the design of the Gira TX_44 design line.
- Torsion-resistant surface-mounted housing due to aluminium profile.
- Frame made of shatter-proof thermoplastic with high resistance to ultraviolet light as well as a scratch-resistant, care-free surface.
- Theft protection ensured by screws with hexalobular socket.
- Signal transmission and supply of the audio and video components via reverse-polarity-protected and short-circuit-proof 2-wire bus.
- One-man commissioning with simple commissioning procedure.
- Weather-resistant loudspeaker.
- High-quality electret microphone.
- Hands-free feature (voice-controlled talk-back with echo and background noise suppression).
- Acknowledgement tone when call button is pressed.
- Voice volume adjustable.
- White call-button illumination with LED technology. Even, clearly visible call button illumination is achieved via maintenance-free, energy-saving LED technology.
- Sprayed-water proof call-button cover plate made of shock-resistant plastic.
- Name plate of the call button can be exchanged without tools and frame removal.
- Professional inscription by the Gira inscription servicewww.beschriftung.gira.deor the Gira inscription software.
- Low installation height of just 19 mm.

**Technical data**

| | |
|---|---|
| Power supply: | DC 26 V ± 2 V (by 2-wire bus) |
| Connections | |
| - 2-wire bus: | 2 x screw terminal |

Illustrations are similar and may deviate from originals.
Prices valid for United Kingdom with prices valid 01/26.

© Copyright by
Gira Giersiepen GmbH & Co. KG
All rights reserved



| | |
|---|---|
| - Additional power supply: | 2 x screw terminal |
| Protection class: | IP44 |
| Ambient temperature: | -25 °C to +70 °C |
| Dimensions | |
| - Door station, 1-gang: | W 110 x H 181 x D 19 mm |
| - Name plate: | W 62 x H 62 mm |

---