


## Power supply DC 24 V 300 mA



Spezifikation	Bestell-Nr.	VE	GBP/Stück o. MWSt.	PS	EAN
 DRA	1296 00	1	87.05	18	4010337296003

### Merkmale

- Power supply DC 24 V for external supply to the Gira One server.

### Technische Daten

Rated voltage	
- Primary:	AC 230 V, 50/60 Hz
Secondary rated voltage	
- Secondary:	DC 24 V
Secondary rated current:	0.3 A
Fuse:	Fine wire fuse 250 V, T 125 mA
Ambient temperature:	-5 °C to +40 °C
Protection class:	IP 20

### Abmessungen

Teilungseinheiten (TE):	4
-------------------------	---