



Gira energy profile with light element and 3 empty units height 769 mm not equipped



| Spezifikation | Bestell-Nr. | VE | GBP/Stück o. MWSSt. | PS | EAN |
|--|-------------|----|---------------------|----|---------------|
|  anthracite | 1349 28 | - | - | - | 4010337349280 |
|  colour aluminium | 1349 26 | - | - | - | 4010337349266 |

Gira energy profile and light profiles with or without light elements for outdoor use. The profiles are made of powder-coated aluminium. For profiles of up to 1400 mm, the base elements are also made of powder-coated aluminium. For profiles of 1400 mm or more, the base elements are made of powder-coated steel. In each case, in the colour anthracite in accordance with the GSB standard. The surface is resistant to weather, UV, soiling, and scratching.

Merkmale

- Freely configurable Gira energy profile with 3 empty units and light element.
- The light element consists of an aluminium reflector and an impact-resistant acrylic glass plate.
- Light is also emitted from the rear as orientation lighting.
- The three empty units can be individually equipped with device inserts from the TX_44 design line or from System 55 by the customer.

Technische Daten

| | |
|--|-------------------------|
| Protection type (device cover closed): | IP44 |
| Dimensions | |
| - Base: | W 229 x H 10 x D 155 mm |
| - Profile: | W 142 x H 769 x D 75 mm |

Hinweise

- For profile heights up to 1400 mm, an optional ground anchor can be used to facilitate mounting on a stone or concrete base.
 - For profile heights of more than 1400 mm, mounting on stone or concrete is only possible using 3 heavy-duty wall anchor.
 - Recommendation: Mount an RCCB prior to the device.
 - Single wall plug mounting.
 - Suitable for E27 light sources with energy efficiency classes A++ to E.
-

Lieferumfang

- Cover frame, 3-gang TX_44 is included with delivery.
 - The mounting materials are included with delivery.
 - Light sources are not included with delivery.
-