



Gira energy profile with 4 empty units height 1400 mm not equipped



| Spezifikation | Bestell-Nr. | VE | GBP/Stück o. MWSt. | PS | EAN |
|--|-------------|----|--------------------|----|---------------|
|  anthracite | 1354 28 | 1 | 977.78 | 17 | 4010337354284 |
|  colour aluminium | 1354 26 | 1 | 1,045.47 | 17 | 4010337354260 |

Gira energy profile and light profiles with or without light elements for outdoor use. The profiles are made of powder-coated aluminium. For profiles of up to 1400 mm, the base elements are also made of powder-coated aluminium. For profiles of 1400 mm or more, the base elements are made of powder-coated steel. In each case, in the colour anthracite in accordance with the GSB standard. The surface is resistant to weather, UV, soiling, and scratching.

Merkmale

- Freely configurable Gira energy profile with 4 empty units.
- The four empty units can be individually equipped with device inserts from the Gira TX_44 design line or from System 55 by the customer.

Technische Daten

| | |
|--|--------------------------|
| Protection type (device cover closed): | IP44 |
| Dimensions | |
| - Base: | W 229 x H 10 x D 155 mm |
| - Profile: | W 142 x H 1400 x D 75 mm |

Hinweise

- For profile heights up to 1400 mm, an optional ground anchor can be used to facilitate mounting on a stone or concrete base.
 - For profile heights of more than 1400 mm, mounting on stone or concrete is only possible using 3 heavy-duty wall anchor.
 - Recommendation: Mount an RCCB prior to the device.
 - Mounting using three heavy-duty wall anchors.
 - Any required electrical isolation of mains and low voltage can be implemented with the included accessories.
-

Lieferumfang

- Gira TX_44 cover frame, 4-gang included with delivery.
 - The mounting materials are included with delivery.
-