


IP interface for KNX



| Spezifikation | Bestell-Nr. | VE | GBP/Stück o. MWSt. | PS | EAN |
|---|-------------|----|--------------------|----|---------------|
|  DRA | 2168 00 | 1 | 238.45 | 26 | 4010337084457 |

Merkmale

- For coupling a PC to the KNX bus to address, program, or diagnose KNX components.

Technische Daten

| | |
|----------------------|---|
| KNX medium: | KNXnet/IP and TP1-256 |
| Rated voltage: | DC 24 to 30 V |
| IP communication: | Ethernet 10/100 BaseT (10/100 Mbit/s) |
| Supported protocols: | ARP, ICMP, IGMP, DHCP, AutoIP, UDP/IP (Core, Tunnelling, Device Management) |
| Connections | |
| - IP: | 2 x RJ45 jacks |
| - KNX: | Connection and junction terminal |
| Ambient temperature: | 0 °C to +45 °C |

Hinweise

- Power supply via external DC 24 V or via unchoked output of the Gira power supply for KNX.

Abmessungen

| | |
|-------------------------|---|
| Teilungseinheiten (TE): | 2 |
|-------------------------|---|