© Copyright by
Gira Giersiepen GmbH & Co. KG
All rights reserved

Thermal servo 230 V~



Specification	Order No.	Packing unit	GBP/piece without VAT	PS	EAN
	2169 00	1	47.28	06	4010337016724

Features

- Thermal valve drive for actuating heating valves for single-room control.
- Compatible with valve adapter system and the connection cable of the predecessor.
- Status display for open or closed.
- First-open function for simple installation and commissioning.
- Closed when de-energised.

Technical data

Operating voltage:	AC 230 V, 50/60 Hz
Operating efficiency:	approx. 1 W
Valve stroke:	4 mm
Ambient temperature:	0 °C to 60 °C
Regulating power:	100 N
Protection class:	IP54
Connection cable	
- Cross section:	2 x 0.75 mm²
- Length:	1 m
Dimensions	
- W x H x D:	58 x 58 x 45 mm

Illustrations are similar and may deviate from originals.
Prices valid for United Kingdom with prices valid 01/26.

© Copyright by
Gira Giersiepen GmbH & Co. KG
All rights reserved

Scope of supply

- Valve adapters VA 80 for the following corner valves are included with delivery. Heimeier, MNG (from 1998), Oventrop M30x1.5 (from 1997), Oventrop Cocon Q, Onda, Schlösser (from 1993), Comap M30x1.5, Tour & Andersson (from 1999), IVAR, Strawa (new bracket from 2003), Taco (for Alpha drive from 2005), Emmeti, Caleffi distributor series 670, Bianchi 4-way valve, Nereus corner valve DN 10.