





Speaker flush-mounted radio IP



Spezifikation	Bestell-Nr.	VE	GBP/Stück o. MWSt.	PS	EAN
 cream white glossy	2282 01	1	25.60	03	4010337076230
 pure white glossy	2282 03	1	25.60	03	4010337076247
 pure white matt	2282 27	1	25.60	03	4010337076254
 anthracite	2282 28	1	27.56	03	4010337076261
 colour aluminium	2282 26	1	30.02	03	4010337076162
 black matt	2282 005	1	30.02	03	4010337037286
 grey matt	2282 015	1	30.02	03	4010337083931
 stainless steel	2282 600	1	34.45	03	4010337032861

Merkmale

- Speaker for connection to the Gira flush-mounted radio.

Technische Daten

Installation depth:	32 mm
Connection cross section - Speaker/AUX connection:	1.5 mm ²
Impedance:	8 Ω
Ambient temperature:	-5 °C to +50 °C
