

Speaker flush-mounted radio IP



Specification	Order No.	Packing unit	GBP/piece without VAT	PS	EAN
 cream white glossy	2282 01	1	25.60	03	4010337076230
 pure white glossy	2282 03	1	25.60	03	4010337076247
 pure white matt	2282 27	1	25.60	03	4010337076254
 anthracite	2282 28	1	27.56	03	4010337076261
 colour aluminium (lacquered)	2282 26	1	30.02	03	4010337076162
 black matt (lacquered)	2282 005	1	30.02	03	4010337037286
 grey matt (lacquered)	2282 015	1	30.02	03	4010337083931
 stainless steel	2282 600	1	34.45	03	4010337032861
 black glass appearance	2282 05	1	34.45	03	4010337889182

Features

- Speaker for connection to the Gira flush-mounted radio.

Technical data

Installation depth:	32 mm
Connection cross section	
- Speaker/AUX connection:	1.5 mm ²
Impedance:	8 Ω
Ambient temperature:	-5 °C to +50 °C
