© Copyright by
Gira Giersiepen GmbH & Co. KG
All rights reserved

USB power supply insert, 2-gang Type A / type C



Specification	Order No.	Packing unit	GBP/piece without VAT	PS	EAN
 white	2349 00	1/5	68.98	02	4010337104681
 black	2369 00	-	-	-	4010337075905

Features

- Charging option for up to two end devices simultaneously using USB cable type A and type C.
- Suitable as a charging device, e.g. for mobile telephones and similar devices.

Technical data

Charging current:	max. 3 A
Rated voltage - Primary: - Secondary:	 AC 100 – 240 V, 50/60 Hz 5 V (± 5%)
Standby:	≤ 0.15 W
Installation depth:	32 mm
Ambient temperature:	+10 °C to +40 °C
Efficiency:	≥ 75%
Compliant with standards:	DIN EN 60950-1/A2

Illustrations are similar and may deviate from originals.
Prices valid for United Kingdom with prices valid 01/26.

© Copyright by
Gira Giersiepen GmbH & Co. KG
All rights reserved

Scope of supply

- USB cables are not included with delivery.
