© Copyright by
Gira Giersiepen GmbH & Co. KG
All rights reserved

www.gira.com

Compensation module LED



Specification	Order No.	Packing unit	GBP/piece without VAT	PS	EAN
	2375 00	1/5	32.60	02	4010337031369

Features

- Enables dimmable HV LED lamps to be operated together with Gira Tronic dimmers or Gira universal dimmers.
- Prevents HV LED lamps in leading edge Gira Tronic and Gira universal dimmers, and in switches with a lighting element of up to 3 mA, from glowing when switched off.
- Improves the dimming behaviour of HV LED lamps in trailing edge Gira Tronic and Gira universal dimmers.

Technical data

Rated voltage:	AC 230 V, 50/60 Hz
Power loss:	max. 2 W
Housing temperature:	max. +65 °C (tc)
Cable length:	approx. 15 cm
Dimensions - W x H x D:	43 x 11.5 x 28.5 mm

Notes

- Can also be used for the dimmers already installed by the customer0305 00and2390 00.

Illustrations are similar and may deviate from originals.
Prices valid for United Kingdom with prices valid 01/26.