


## Network connection box insert cat.6A, 2-gang Insulation displacement connectors



Spezifikation	Bestell-Nr.	VE	GBP/Stück o. MWSt.	PS	EAN
	2452 00	1	39.33	01	4010337881797

### Merkmale

- Shielded network connection box cat.6A with two RJ45 jacks (8/8) for data transfer rates up to 10 Gbit-Ethernet in accordance with IEEE 802.3an.
- 45° angled socket outlet for parapet trunking, floor tank and flush-mounted installation.
- Cable entry possible from all directions in 8 x 45° increments.

### Technische Daten

Installation depth: 33 mm

### Hinweise

- For screw attachment only.