







SCHUKO socket outlet, 16 A 250 V~ with increased contact protection (Safety Plus) and USB power supply, 2-gang Type A / type C



| Spezifikation | Bestell-Nr. | VE | GBP/Stück o. MWSt. | PS | EAN |
|---|-------------|----|--------------------|----|---------------|
|  cream white glossy | 2459 01 | 1 | 81.93 | 02 | 4010337076223 |
|  pure white glossy | 2459 03 | 1 | 81.93 | 02 | 4010337076179 |
|  pure white matt | 2459 27 | 1 | 81.93 | 02 | 4010337076186 |
|  anthracite | 2459 28 | 1 | 83.36 | 02 | 4010337076285 |
|  colour aluminium | 2459 26 | 1 | 90.22 | 02 | 4010337076193 |
|  black matt | 2459 005 | 1 | 90.22 | 02 | 4010337076209 |
|  grey matt | 2459 015 | 1 | 90.22 | 02 | 4010337090151 |
|  stainless steel (lacquered) | 2459 600 | 1 | 90.22 | 02 | 4010337076148 |

Merkmale

- Charging option for up to two end devices simultaneously using USB cable type A and type C.
 - Up to two end devices can be charged simultaneously.
-

Technische Daten

| | |
|--------------------------|--|
| Input voltage: | AC 220 – 250 V, 50/60 Hz |
| USB connection: | 1 x type A, 1 x type C |
| Output voltage USB: | DC 5 V |
| Charging current | |
| - USB A: | max. 2.4 A |
| - USB C: | Max. 3 A |
| Standby: | ≤80 mW |
| Connection cross section | |
| - for conductors from: | 1.5 mm ² to 2.5 mm ² |
| Installation depth: | 31 mm |
| Ambient temperature: | +5° C to +35° C |

Hinweise

- Increased contact protection (Safety Plus) in accordance with DIN VDE 0620-1.
 - During long charging cycles, the housing of the product may heat up.
 - Using a deep device box is recommended.
-

Lieferumfang

- Type A or type C USB cables are not included with delivery.
-