© Copyright by
Gira Giersiepen GmbH & Co. KG
All rights reserved

Bluetooth® wall transmitter, 1-gang



Specification	Order No.	Packing unit	GBP/piece without VAT	PS	EAN
cream white glossy	2461 01	1	99.45	02	4010337110712
pure white glossy	2461 03	1	99.45	02	4010337101598
pure white matt	2461 27	1	99.45	02	4010337101604
anthracite	2461 28	1	101.75	02	4010337101611
colour aluminium (lacquered)	2461 26	1	105.21	02	4010337101628
black matt (lacquered)	2461 005	1	105.21	02	4010337101635
grey matt (lacquered)	2461 015	1	105.21	02	4010337110729

Features

- Wireless transmitter for transmitting switching, dimming or blind commands to the Bluetooth® wireless receivers from the System 3000 or third parties, e.g Casambi.
- Battery-free device without external power supply. The transmission energy is generated from mechanical energy by actuating the rocker.
- Configuration via the app or NFC.

Illustrations are similar and may deviate from originals.
Prices valid for United Kingdom with prices valid 01/26.

© Copyright by
Gira Giersiepen GmbH & Co. KG
All rights reserved

Technical data

Wireless frequency:	2.402 - 2.480 GHz
Wireless protocol:	Bluetooth® low energy (BLE)
Interface:	NFC
Range	
- in free field:	up to 75 m
- in buildings:	approx. 10 m
Ambient temperature:	-25 °C to +65 °C
Humidity:	0 to 95 % (without condensation)

Notes

- Mounting on device box or on smooth, level surfaces using screws or adhesives.
- This product cannot be used with eNet.

Scope of supply

- Radio wall transmitter, comes with mounting plate, adhesive film (privacy protection for glass surfaces), and adhesive points for installation on smooth, level surfaces.
