© Copyright by
Gira Giersiepen GmbH & Co. KG
All rights reserved

www.gira.com

Terminal strip, 6-gang 230 V~



Specification	Order No.	Packing unit	GBP/piece without VAT	PS	EAN
	2479 00	1	92.03	02	4010337110187

Features

- Terminal strip for wiring room temperature controllers and thermal servos.

Technical data

Power consumption:	230 V, 50 VA
Fuse	
- 230 V:	T4AH
Quantity	
- Heating zones:	6
- Room temperature controller:	Max. 6
- Servos:	Max. 12
Switch-on current	
- Per servo:	Max. 500 mA
Rated load	
- All drives:	Max. 24 W
Switching capacity	
- Pump control:	2 A / 200 VA inductive
Connections	
- Pump control:	1
- Heating/cooling switchover:	1
- External timer:	1
- Room temperature controller:	6
- 230 V power supply:	1
Direction of action:	NC
Mode of operation:	Type 1/1.C

Illustrations are similar and may deviate from originals.
Prices valid for United Kingdom with prices valid 01/26.

© Copyright by
Gira Giersiepen GmbH & Co. KG
All rights reserved

Protection class:	II
Ambient humidity:	80% non-condensing
Ambient temperature:	0 to +50°C
Clampable conductor cross-section:	0.2 bis 1.5 mm²
Dimensions - W x H x D:	326.5 x 90 x 50 mm