


Kaiser diamond abrasive crown without dust extraction



Spezifikation	Bestell-Nr.	VE	GBP/Stück o. MWSSt.	PS	EAN
	2489 00	-	-	-	4010337031314

Merkmale

- Thread for screwing on the direct attachment or chuck adapter M18 x 1.5.

Technische Daten

Drill Ø: 82 mm
Working depth: Max. 70 mm

Hinweise

- Kaiser order no. 1088-00