


Kaiser turbo cutter MULTI 4000



Spezifikation	Bestell-Nr.	VE	GBP/Stück o. MWSt.	PS	EAN
	2497 00	-	-	-	4010337031239

Merkmale

- High cutting capacity.
- Precise cut for circular drill holes.
- High rotating accuracy.
- Removable edge countersink.
- Suitable for all drills with 13 mm drill chuck.
- With edge countersink and PCB ejector.

Technische Daten

Drill hole Ø:	68 mm
Drill hole depth:	36 mm

Hinweise

- Kaiser Order No. 1083-10