© Copyright by
Gira Giersiepen GmbH & Co. KG
All rights reserved

www.gira.com

Power supply DC 24 V 700 mA



Specification	Order No.	Packing unit	GBP/piece without VAT	PS	EAN
 DRA	2570 00	1	101.87	18	4010337025702

Technical data

Rated voltage - Primary:	AC 230 V, 50 Hz
Secondary rated voltage - Secondary:	DC 24 V SELV
Secondary rated current:	0.7 A
Fuse:	Electronic self-resetting
Ambient temperature:	-5 °C to +40 °C

Dimensions

Modular width (MW):	6

Illustrations are similar and may deviate from originals.
Prices valid for United Kingdom with prices valid 01/26.