


DCS repeater



Spezifikation	Bestell-Nr.	VE	GBP/Stück o. MWSt.	PS	EAN
 DRA	2572 00	1	317.49	10	4010337011125

Merkmale

- Active component for upgrading a Gira door communication system with an audio and video function.
- Range extension and increase of the number of devices when using additional control devices.
- Amplification of the audio and data signals for the door communication system in both directions.

Repeater mode

- Interconnects two line segments, to double both the number of devices in a video or audio door communication system and the cable range.
- Important: An additional control device is required to supply the second line segment.

Multi-conversation mode

- In multi-conversation mode, the complete system is subdivided into several lines (one main line, up to five ancillary lines) interconnected via the DCS repeater.
- Power is supplied to each line by its own control device.
- Up to five DCS repeaters can be used in one system in multi-conversation mode.

Technische Daten

Power supply:	via the 2-wire bus
Connections	
- 2-wire bus IN:	2 x plug terminal
- 2-wire bus OUT:	2 x plug terminal
Memory card:	microSD card (SDHC) up to max. 32 GB
Ambient temperature:	-5 °C to +45 °C

Hinweise

- Data backupThe configuration of the DCS repeater can be backed up to a microSD card.
 - Start-upStart-up of the DCS repeater is also possible without a microSD card.
-

Lieferumfang

- The microSD card is not included with delivery.
-

Abmessungen

Teilungseinheiten (TE): 2
