









British Standard socket outlet (BS 546) Round Pin 15 A 250 V~ with shutter System 55



| Spezifikation | Bestell-Nr. | VE | GBP/Stück o. MWSt. | PS | EAN |
|---|-------------|------|--------------------|----|---------------|
|  cream white glossy | 2774 01 | 1/10 | 17.22 | 29 | 4010337079200 |
|  pure white glossy | 2774 03 | 1/10 | 17.22 | 29 | 4010337079217 |
|  anthracite | 2774 28 | 1/10 | 19.58 | 29 | 4010337079231 |
|  colour aluminium | 2774 26 | 1/10 | 23.09 | 29 | 4010337079224 |
|  black matt | 2774 005 | 1/10 | 23.09 | 29 | 4010337037781 |
|  grey matt | 2774 015 | 1/10 | 17.22 | 29 | 4010337086284 |
|  stainless steel (lacquered) | 2774 600 | 1/10 | 26.35 | 29 | 4010337022152 |

Merkmale

- With screw terminals.
- For screw attachment only.

Technische Daten

Installation depth: 20 mm

Connection cross section
- maximum: 2 x 4 mm²
