









## British Standard socket outlet (BS 1363), 13 A 250 V~ switched, with shutter System 55



Spezifikation	Bestell-Nr.	VE	GBP/Stück o. MWSt.	PS	EAN
 cream white glossy	2778 01	1/10	19.48	29	4010337079477
 pure white glossy	2778 03	1/10	19.48	29	4010337079484
 anthracite	2778 28	1/10	21.92	29	4010337079507
 colour aluminium	2778 26	1/10	25.68	29	4010337079491
 black matt	2778 005	1/10	25.68	29	4010337037750
 grey matt	2778 015	1/10	25.68	29	4010337086390
 stainless steel (lacquered)	2778 600	1/10	29.18	29	4010337022091

### Merkmale

- With screw terminals.

## Technische Daten

Installation depth: 20 mm

---

## Hinweise

- For screw attachment only.
  - Other functions and variants, including for the 80 mm BS socket, available upon request.
-