








British Standard socket outlet (BS 1363-2) 13 A 250 V~ switched, with control light and shutter System 55



Spezifikation	Bestell-Nr.	VE	GBP/Stück o. MWSt.	PS	EAN
 cream white glossy	2780 01	1/10	20.90	29	4010337079590
 pure white glossy	2780 03	1/10	20.90	29	4010337079606
 anthracite	2780 28	1/10	26.75	29	4010337079620
 colour aluminium	2780 26	1/10	30.04	29	4010337079613
 black matt	2780 005	1/10	30.04	29	4010337037767
 grey matt	2780 015	1/10	30.04	29	4010337086406
 stainless steel (lacquered)	2780 600	1/10	30.02	29	4010337022114

Merkmale

- With screw terminals.
- For screw attachment only.

Technische Daten

Installation depth: 20 mm
