© Copyright by
Gira Giersiepen GmbH & Co. KG
All rights reserved



**British Standard socket outlet (BS 1363-2) 13 A 250 V~ switched, with control light and shutter System 55**




| Specification | Order No. | Packing unit | GBP/piece without VAT | PS | EAN |
|---|---|---|---|---|---|
|  cream white glossy | 2780 01 | 1/10 | 20.90 | 29 | 4010337079590 |
|  pure white glossy | 2780 03 | 1/10 | 20.90 | 29 | 4010337079606 |
|  anthracite | 2780 28 | 1/10 | 26.75 | 29 | 4010337079620 |
|  colour aluminium (lacquered) | 2780 26 | 1/10 | 30.04 | 29 | 4010337079613 |
|  black matt (lacquered) | 2780 005 | 1/10 | 30.04 | 29 | 4010337037767 |
|  grey matt (lacquered) | 2780 015 | 1/10 | 30.04 | 29 | 4010337086406 |
|  stainless steel (lacquered) | 2780 600 | 1/10 | 30.02 | 29 | 4010337022114 |

**Features**

- With screw terminals.
- For screw attachment only.

Illustrations are similar and may deviate from originals.
Prices valid for United Kingdom with prices valid 01/26.

© Copyright by
Gira Giersiepen GmbH & Co. KG
All rights reserved



**Technical data**

| | |
|---|---|
| Installation depth: | 20 mm |