








British Standard double socket outlet (BS 1363-2) 13 A 250 V~ with shutter Support ring 80 x 132 mm



Spezifikation	Bestell-Nr.	VE	GBP/Stück o. MWSt.	PS	EAN
 cream white glossy	2782 01	1/5	18.12	29	4010337079729
 pure white glossy	2782 03	1/5	18.12	29	4010337079736
 anthracite	2782 28	1/5	20.45	29	4010337079750
 colour aluminium	2782 26	1/5	24.01	29	4010337079743
 black matt	2782 005	1/5	24.01	11	4010337036470
 grey matt	2782 015	1/5	24.01	11	4010337086413
 stainless steel (lacquered)	2782 600	1/5	27.24	29	4010337022138

Merkmale

- With screw terminals.
- For screw attachment only.

Technische Daten

Installation depth: 20 mm

Connection cross section
- maximum: $2 \times 4 \text{ mm}^2 + 2.5 \text{ mm}^2$
