








British Standard double socket outlet (BS 1363-2) 13 A 250 V~ switched, with shutter Support ring 80 x 132 mm



Spezifikation	Bestell-Nr.	VE	GBP/Stück o. MWSt.	PS	EAN
 cream white glossy	2783 01	1/5	19.71	29	4010337079798
 pure white glossy	2783 03	1/5	19.71	29	4010337079804
 anthracite	2783 28	1/5	22.06	29	4010337079828
 colour aluminium	2783 26	1/5	25.57	29	4010337079811
 black matt	2783 005	1/5	25.57	11	4010337036494
 grey matt	2783 015	1/5	25.57	11	4010337086420
 stainless steel (lacquered)	2783 600	1/5	28.84	29	4010337022145

Merkmale

- With screw terminals.
- For screw attachment only.

Technische Daten

Installation depth: 20 mm
