© Copyright by
Gira Giersiepen GmbH & Co. KG
All rights reserved

www.gira.com

British Standard double socket outlet (BS 1363-2) 13 A 250 V~ switched, with control light and shutter Support ring 80 x 132 mm



Specification	Order No.	Packing unit	GBP/piece without VAT	PS	EAN
 cream white glossy	2784 01	1/5	24.40	29	4010337079859
 pure white glossy	2784 03	1/5	24.40	29	4010337079866
 anthracite	2784 28	1/5	26.74	29	4010337079880
 colour aluminium (lacquered)	2784 26	1/5	30.25	29	4010337079873
 black matt (lacquered)	2784 005	1/5	30.25	11	4010337036487
 grey matt (lacquered)	2784 015	1	30.25	11	4010337086758
 stainless steel (lacquered)	2784 600	1/5	33.52	29	4010337022176

Features

- With screw terminals.
- For screw attachment only.

Illustrations are similar and may deviate from originals.
Prices valid for United Kingdom with prices valid 01/26.

© Copyright by
Gira Giersiepen GmbH & Co. KG
All rights reserved

Technical data

Installation depth:	20 mm