








**British Standard double socket outlet (BS 1363-2) 13 A 250 V~ switched, with control light and shutter Support ring 80 x 132 mm**



Spezifikation	Bestell-Nr.	VE	GBP/Stück o. MWSt.	PS	EAN
 cream white glossy	2784 01	1/5	24.40	29	4010337079859
 pure white glossy	2784 03	1/5	24.40	29	4010337079866
 anthracite	2784 28	1/5	26.74	29	4010337079880
 colour aluminium	2784 26	1/5	30.25	29	4010337079873
 black matt	2784 005	1/5	30.25	11	4010337036487
 grey matt	2784 015	1	30.25	11	4010337086758
 stainless steel (lacquered)	2784 600	1/5	33.52	29	4010337022176

## Merkmale

- With screw terminals.
- For screw attachment only.

## Technische Daten

Installation depth: 20 mm

---