







British Standard double socket outlet (BS 1363-2) 13 A 250 V~ switched, with control light and shutter Support ring 80 x 132 mm



| Spezifikation | Bestell-Nr. | VE | GBP/Stück o. MWSt. | PS | EAN |
|---|-------------|-----|--------------------|----|---------------|
|  cream white glossy | 2784 01 | 1/5 | 24.40 | 29 | 4010337079859 |
|  pure white glossy | 2784 03 | 1/5 | 24.40 | 29 | 4010337079866 |
|  anthracite | 2784 28 | 1/5 | 26.74 | 29 | 4010337079880 |
|  colour aluminium | 2784 26 | 1/5 | 30.25 | 29 | 4010337079873 |
|  black matt | 2784 005 | 1/5 | 30.25 | 11 | 4010337036487 |
|  grey matt | 2784 015 | 1 | 30.25 | 11 | 4010337086758 |
|  stainless steel (lacquered) | 2784 600 | 1/5 | 33.52 | 29 | 4010337022176 |

Merkmale

- With screw terminals.
- For screw attachment only.

Technische Daten

Installation depth: 20 mm
