

## British Standard Fused spur connection unit (BS 1363-4) 13 A 250 V~ switched System 55



| Spezifikation                                                                                                   | Bestell-Nr. | VE  | GBP/Stück o. MWSt. | PS | EAN           |
|-----------------------------------------------------------------------------------------------------------------|-------------|-----|--------------------|----|---------------|
|  cream white glossy            | 2785 01     | 1/5 | 21.09              | 29 | 4010337079910 |
|  pure white glossy           | 2785 03     | 1/5 | 21.09              | 29 | 4010337079927 |
|  anthracite                  | 2785 28     | 1/5 | 23.41              | 29 | 4010337079941 |
|  colour aluminium            | 2785 26     | 1/5 | 26.96              | 29 | 4010337079934 |
|  black matt                  | 2785 005    | 1/5 | 26.96              | 29 | 4010337037101 |
|  grey matt                   | 2785 015    | 1/5 | 26.96              | 29 | 4010337086994 |
|  stainless steel (lacquered) | 2785 600    | 1/5 | 30.18              | 29 | 4010337022244 |

### Merkmale

- With screw terminals.
- For screw attachment only.

## Technische Daten

|                                        |                         |
|----------------------------------------|-------------------------|
| Installation depth:                    | 29 mm                   |
| Connection cross section<br>- maximum: | 2 x 2.5 mm <sup>2</sup> |

---