








British Standard Fused spur connection unit (BS 1363-4) 13 A 250 V~ switched System 55



Spezifikation	Bestell-Nr.	VE	GBP/Stück o. MWSt.	PS	EAN
 cream white glossy	2785 01	1/5	21.09	29	4010337079910
 pure white glossy	2785 03	1/5	21.09	29	4010337079927
 anthracite	2785 28	1/5	23.41	29	4010337079941
 colour aluminium	2785 26	1/5	26.96	29	4010337079934
 black matt	2785 005	1/5	26.96	29	4010337037101
 grey matt	2785 015	1/5	26.96	29	4010337086994
 stainless steel (lacquered)	2785 600	1/5	30.18	29	4010337022244

Merkmale

- With screw terminals.
- For screw attachment only.

Technische Daten

Installation depth: 29 mm

Connection cross section
- maximum: 2 x 2.5 mm²
