








British Standard Fused spur connection unit (BS 1363-4) 13 A 250 V~ switched System 55



| Spezifikation | Bestell-Nr. | VE | GBP/Stück o. MWSt. | PS | EAN |
|---|-------------|-----|--------------------|----|---------------|
|  cream white glossy | 2785 01 | 1/5 | 21.09 | 29 | 4010337079910 |
|  pure white glossy | 2785 03 | 1/5 | 21.09 | 29 | 4010337079927 |
|  anthracite | 2785 28 | 1/5 | 23.41 | 29 | 4010337079941 |
|  colour aluminium | 2785 26 | 1/5 | 26.96 | 29 | 4010337079934 |
|  black matt | 2785 005 | 1/5 | 26.96 | 29 | 4010337037101 |
|  grey matt | 2785 015 | 1/5 | 26.96 | 29 | 4010337086994 |
|  stainless steel (lacquered) | 2785 600 | 1/5 | 30.18 | 29 | 4010337022244 |

Merkmale

- With screw terminals.
- For screw attachment only.

Technische Daten

Installation depth: 29 mm

Connection cross section
- maximum: 2 x 2.5 mm²
