

British Standard fused spur connection unit (BS 1363-4) 13 A 250 V~ switched, with control light System 55



Spezifikation	Bestell-Nr.	VE	GBP/Stück o. MWSt.	PS	EAN
 cream white glossy	2787 01	1/5	35.25	29	4010337080053
 pure white glossy	2787 03	1/5	35.25	29	4010337080060
 anthracite	2787 28	1/5	37.56	29	4010337080084
 colour aluminium	2787 26	1/5	41.11	29	4010337080077
 black matt	2787 005	1/5	41.11	29	4010337037118
 grey matt	2787 015	1/5	41.11	29	4010337087052
 stainless steel (lacquered)	2787 600	1/5	44.34	29	4010337022190

Merkmale

- With screw terminals.
- For screw attachment only.

Technische Daten

Installation depth: 29 mm
