








Razor socket outlet (DIN EN 61558 2-5) 115 - 230 V~ for cover frame, 2-gang without crossbar System 55



Spezifikation	Bestell-Nr.	VE	GBP/Stück o. MWSt.	PS	EAN
 cream white glossy	2820 01	1	108.79	29	4010337016755
 pure white glossy	2820 03	1	108.79	29	4010337016762
 anthracite	2820 28	1	111.13	29	4010337016809
 colour aluminium	2820 26	1	114.62	29	4010337016793
 black matt	2820 005	1	114.62	29	4010337037323
 grey matt	2820 015	1	114.62	29	4010337087090
 stainless steel (lacquered)	2820 600	1	124.79	29	4010337021995