

## British Standard switch (BS EN 60669-1) 45 A 250 V~ Circuit breaker, 2-pole



| Spezifikation                                                                                                   | Bestell-Nr. | VE   | GBP/Stück o. MWSt. | PS | EAN           |
|-----------------------------------------------------------------------------------------------------------------|-------------|------|--------------------|----|---------------|
|  cream white glossy            | 2821 01     | 1/10 | 32.67              | 29 | 4010337035886 |
|  pure white glossy           | 2821 03     | 1/10 | 32.67              | 29 | 4010337035893 |
|  anthracite                  | 2821 28     | 1/10 | 35.08              | 29 | 4010337035909 |
|  colour aluminium            | 2821 26     | 1/10 | 38.75              | 29 | 4010337035916 |
|  black matt                  | 2821 005    | 1/10 | 38.75              | 29 | 4010337053361 |
|  grey matt                   | 2821 015    | 1/10 | 38.75              | 29 | 4010337087106 |
|  stainless steel (lacquered) | 2821 600    | -    | -                  | -  | 4010337035930 |

### Technische Daten

|                                                     |                                                 |
|-----------------------------------------------------|-------------------------------------------------|
| Installation depth:                                 | 16 mm                                           |
| Connection cross section<br>- for conductors up to: | 2 x 6 mm <sup>2</sup> or 1 x 10 mm <sup>2</sup> |

## Hinweise

- Individual device. Cannot be combined.

---