

British Standard switch (BS EN 60669-1) 45 A 250 V~ Circuit breaker, 2-pole



Spezifikation	Bestell-Nr.	VE	GBP/Stück o. MWSt.	PS	EAN
 cream white glossy	2821 01	1/10	32.67	29	4010337035886
 pure white glossy	2821 03	1/10	32.67	29	4010337035893
 anthracite	2821 28	1/10	35.08	29	4010337035909
 colour aluminium	2821 26	1/10	38.75	29	4010337035916
 black matt	2821 005	1/10	38.75	29	4010337053361
 grey matt	2821 015	1/10	38.75	29	4010337087106
 stainless steel (lacquered)	2821 600	-	-	-	4010337035930

Technische Daten

Installation depth:	16 mm
Connection cross section - for conductors up to:	2 x 6 mm ² or 1 x 10 mm ²

Hinweise

- Individual device. Cannot be combined.
