








## Rocker switch, 3-gang, 10 AX 250 V~ with rockers Universal 1-way/2-way switch



Spezifikation	Bestell-Nr.	VE	GBP/Stück o. MWSt.	PS	EAN
 cream white glossy	2832 01	1/10	32.87	29	4010337832010
 pure white glossy	2832 03	1/10	32.87	29	4010337832034
 anthracite	2832 28	1/10	35.33	29	4010337832287
 colour aluminium	2832 26	1/10	39.08	29	4010337832263
 black matt	2832 005	1/10	39.08	11	4010337038528
 grey matt	2832 015	1/10	39.08	11	4010337087120
 stainless steel (lacquered)	2832 600	1/10	42.56	29	4010337022053

### Technische Daten

Installation depth:	25 mm
Connection cross section - for conductors up to:	2.5 mm <sup>2</sup>

# GIRA Parts list

catalogue.gira.com

© Copyright by  
Gira Giersiepen GmbH & Co. KG  
All rights reserved

www.gira.com

## Hinweise

- For screw attachment only.

---